Mustang-T100-T5





Feature

- 5 x Coral Edge TPU™ ML accelerator
- 20 TOPS peak performance (int8)
- Host interface PCIe Gen2 x4
- Low-profile PCle form factor
- Support Multiple card
- Approximate 15W
- RoHS compliants



Specifications

| - | | | | |
|--------------------------|---|--|--|--|
| Model Name | Mustang-T100-T5 | | | |
| Main Chip | Five Coral Edge TPU™ Accelerator Module | | | |
| Operating Systems | Linux: 64-bit version of Debian 10 or Ubuntu 16.04 (or newer) | | | |
| | Windows: 64-bit version of Windows 10 | | | |
| Dataplane Interface | PCI Express Gen2 x4 | | | |
| Power Consumption | Approximate 15W | | | |
| Operating Temperature | -20°C~55°C | | | |
| Cooling Solution | Active | | | |
| Dimensions | Standard half-height, half-length, single-slot PCle card | | | |
| Dip Switch/LED indicator | Identify card number | | | |
| Support Framwork | Tensorflow Lite | | | |
| Precision | INT8 | | | |

Ordering Information

| Part No. | Description |
|---------------------|--|
| Mustang-T100-T5-R10 | TPU Accelerator Card with 5 x Coral edge TPU, PCIe Gen2 x4 interface, RoHS |

Packing List

| 1 x Full height bracket | | | |
|-------------------------|--|--|--|
| 1 x QIG | | | |



Scalable infrastructure, support multiple cards

You can install up to eight Mustang-T100 Al accelerator card in one system to support additional Al workload and expand the Al computing capabilities in any requirement. With switch and LED display, you can track the






>>

Multitasking or Pipelining, Select Your Inferencing Mode

For numerous AI applications at the edge, clients can select from two different modes to run your inferencing project depending on their needs.


Multitasking function to run each model in parallel

If you need to run multiple models, you can assign each model to a specific Edge TPU and run them in parallel at the same time for extreme computing performance.



Model pipelining to get faster throughput and low latency


For other scenarios that require very fast throughput or large models, pipelining your model allows you to execute different segments of the same model on different Edge TPUs. This can improve throughput for high-speed applications and can reduce total latency for large models.



>>

High Compatibility From The Start


To support diverse needs from IT or Al developers, the Mustang-T100 can be implemented in various operating systems, such as Linux, X86, ARM, or small FF to accelerate and maximum edge Al performance. More, combined with TensorFlow Lite, no need to build ML training models from the ground up. TensorFlow Lite models can be compiled models to run on the Edge TPU completely.



Accelerator Module datasheet

- Coral Edge TPU™ ML accelerator: 4 TOPS peak performance (int8) / 2 TOPS per watt
- Integrated power management
- Weight: 0.67 g
- PCle Gen2 x1 or USB 2.0 interface
- Operating temp: -20°C~55°C
- Surface-mounted (LGA) module
- RoHS compliant
- Size: 15.0 x 10.0 x 1.5 mm
- Support ARM (Linux) & X86(Windows & Linux)





Introduction

Coral is a hardware and software platform for building intelligent devices with fast neural network inferencing. At the heart of our devices is the Edge TPU coprocessor. This is a small ASIC built by Google that's specially-designed to execute state-of-the-art neural networks at high speed, with a low power cost.

The Edge TPU is capable of performing 4 trillion operations (tera-operations) per second (TOPS), using 0.5 watts for each TOPS (2 TOPS per watt).

Mustang-T100-T5 Block Diagram

